



Vehiculo	Chasis	Año	HP/kW	Motor
NISSAN BLUEBIRD (T72 , T12, U12) 1.6	Saloon	1986 - 1990	83 / 61	CA16S
NISSAN BLUEBIRD (T72 , T12, U12) 1.6	Saloon	1985 - 1990	90 / 66	CA16S
NISSAN BLUEBIRD (T72 , T12, U12) 1.8 i 16V (RLT72)	Saloon	1989 - 1990	129 / 95	CA18D
NISSAN BLUEBIRD (T72 , T12, U12) 2.0 D (SLT72, T12)	Saloon	1986 - 1990	67 / 49	LD20
NISSAN BLUEBIRD (T72 , T12, U12) 2.0 i	Saloon	1988 - 1990	115 / 85	CA20E
NISSAN BLUEBIRD (U11) 1.8	Saloon	1983 - 1988	90 / 66	CA18S
NISSAN BLUEBIRD (U11) 1.8 Turbo	Saloon	1984 - 1990	135 / 99	CA18T
NISSAN BLUEBIRD (U11) 2.0 D	Saloon	1984 - 1988	58 / 43	LD20
NISSAN BLUEBIRD (U11) 2.0 i	Saloon	1984 - 1988	105 / 77	CA20E
NISSAN BLUEBIRD Hatchback (T72, T12) 1.6	Hatchback	1986 - 1991	90 / 66	CA16S
NISSAN BLUEBIRD Hatchback (T72, T12) 1.6	Hatchback	1986 - 1990	83 / 61	CA16S
NISSAN BLUEBIRD Hatchback (T72, T12) 2.0 D (FSLT72, T12)	Hatchback	1986 - 1990	67 / 49	LD20
NISSAN BLUEBIRD Station Wagon (WU11) 2.0 D	Estate	1986 - 1990	67 / 49	LD20
NISSAN BLUEBIRD Station Wagon (WU11) 2.0 D	Estate	1984 - 1988	58 / 43	LD20
NISSAN BLUEBIRD Station Wagon (WU11) 2.0 i	Estate	1984 - 1990	105 / 77	CA20E
NISSAN BLUEBIRD Station Wagon (WU11) 2.0 i	Estate	1988 - 1990	115 / 85	CA20E
NISSAN PRAIRIE PRO (M11) 2.0	MPV	1989 - 1990	116 / 85	CA20E
NISSAN PRAIRIE PRO (M11) 2.0 4x4	MPV	1989 - 1990	116 / 85	CA20E
NISSAN PRAIRIE PRO (M11) 2.0 i	MPV	1988 - 1992	98 / 72	CA20E
NISSAN PRAIRIE PRO (M11) 2.0 i 4x4	MPV	1988 - 1992	98 / 72	CA20E

Información del Artículo

- Lado de la reuda dentada exterior: 27
- Dientes Internos (Lado de rueda) : 23
- Diametro de sello : 56 mm
- Pre-engrasada

--