



Vehiculo	Chasis	Año	HP/kW	Motor
OPEL CORSA A Box (S83) 1.0 (F08, W5L)	Box	1986 - 1989	45 / 33	10 S
OPEL CORSA A Box (S83) 1.2 (F08, W5L)	Box	1986 - 1990	60 / 44	12 S
OPEL CORSA A Box (S83) 1.2 (F08, W5L)	Box	1986 - 1989	45 / 33	12 NC, E 12 GV
OPEL CORSA A Box (S83) 1.2 (F08, W5L)	Box	1986 - 1989	54 / 40	12 ST
OPEL CORSA A Box (S83) 1.3 (F08, W5L)	Box	1986 - 1989	69 / 51	13 SB
OPEL CORSA A Box (S83) 1.3 (F08, W5L)	Box	1986 - 1989	60 / 44	13 NB
OPEL CORSA A Box (S83) 1.5 D (F08, W5L)	Box	1987 - 1989	50 / 37	15 D (4EC1)
OPEL CORSA A Hatchback (S83) 1.0 (F08, M08, F68, M68)	Hatchback	1982 - 1993	45 / 33	10 S
OPEL CORSA A Hatchback (S83) 1.2 (F08, M08, F68, M68)	Hatchback	1982 - 1990	60 / 44	12 S
OPEL CORSA A Hatchback (S83) 1.2 (F08, M08, F68, M68)	Hatchback	1982 - 1990	45 / 33	12 NC, E 12 GV
OPEL CORSA A Hatchback (S83) 1.2 N (F08, M08, F68, M68)	Hatchback	1990 - 1993	52 / 38	12 NV
OPEL CORSA A Hatchback (S83) 1.2 S (F08, M08, F68, M68)	Hatchback	1982 - 1990	55 / 40	12 ST
OPEL CORSA A Hatchback (S83) 1.2 i (F08, M08, F68, M68)	Hatchback	1989 - 1993	45 / 33	C 12 NZ
OPEL CORSA A Hatchback (S83) 1.3 (F08, M08, F68, M68)	Hatchback	1985 - 1989	60 / 44	13 NB
OPEL CORSA A Hatchback (S83) 1.3 S (F08, M08, F68, M68)	Hatchback	1982 - 1989	70 / 51	13 SB
OPEL CORSA A Hatchback (S83) 1.3 i (F08, M08, F68, M68)	Hatchback	1986 - 1990	60 / 44	C 13 N
OPEL CORSA A Hatchback (S83) 1.4 S (F08, M08, F68, M68)	Hatchback	1990 - 1993	72 / 53	14 NV
OPEL CORSA A Hatchback (S83) 1.4 Si (F08, M08, F68, M68)	Hatchback	1991 - 1993	82 / 60	C 14 SE
OPEL CORSA A Hatchback (S83) 1.4 i (F08, M08, F68, M68)	Hatchback	1990 - 1993	60 / 44	C 14 NZ
OPEL CORSA A Hatchback (S83) 1.4 i (F08, M08, F68, M68)	Hatchback	1985 - 1993	54 / 40	C 14 NZ

Información del Artículo

- Tamaño del Hilo : M20X1
- Lado de la reuda dentada exterior: 22
- Dientes Internos (Lado de rueda) : 28
- Diametro de sello : 52 mm

- Diámetro exterior : 81.4 mm