



Vehiculo	Chasis	Año	HP/kW	Motor
MITSUBISHI COLT I (A15 A) 1.2 GL (A151A)	Hatchback	1978 - 1984	55 / 40	4G11
MITSUBISHI COLT I (A15 A) 1.4 GLX,GT (A152A)	Hatchback	1979 - 1984	70 / 51	4G12
MITSUBISHI COLT I (A15 A) 1.4 Turbo (A152A)	Hatchback	1981 - 1984	105 / 77	4G12 T
MITSUBISHI COLT II (C1 A) 1.6 Turbo ECi (C13A)	Hatchback	1986 - 1988	105 / 77	G32BT
MITSUBISHI COLT II (C1 A) 1.6 Turbo ECi (C13A)	Hatchback	1984 - 1988	125 / 92	4G32 T/C
MITSUBISHI CORDIA (A21 A, AB, AC) 1.6 GSL (A212A)	Coupe	1982 - 1986	75 / 55	4G32
MITSUBISHI GALANT III (E1 A) 1.6 GLX (E11A)	Saloon	1984 - 1990	75 / 55	4G32
MITSUBISHI LANCER F (A15) 1.2 GLX (A171)	Saloon	1983 - 1984	55 / 40	4G11
MITSUBISHI LANCER F (A15) 1.4 GLX (A172)	Saloon	1983 - 1984	70 / 51	4G12
MITSUBISHI LANCER II (A17) 1.4 GLX (A172)	Saloon	1979 - 1983	68 / 50	4G12
MITSUBISHI LANCER III (C1 A, C6 A) 1.5 GLX (C12AS)	Saloon	1983 - 1988	75 / 55	4G15 (8V)
MITSUBISHI LANCER III Station Wagon (C1 V, C3 V) 1.8 4WD (C37V)	Estate	1987 - 1987	90 / 66	4G37
MITSUBISHI LANCER III Station Wagon (C1 V, C3 V) 1.8 4WD (C37V)	Estate	1987 - 1989	83 / 61	G37B

Información del Artículo

- Tamaño del Hilo : M22X1.5
- Lado de la reuda dentada exterior: 25
- Dientes Internos (Lado de rueda) : 22
- Diametro de sello : 50 mm
- Diametro exterior : 78.7 mm